


UTC-P01

2M Camera Module for UTC-500 Series



Specifications

Interface	USB (Cable Length:50cm)
Focusing Range	DOF on 40 ~ 80 cm; Supports auto focus
Frame Rate	500Lux Frame rate: 640 x 480 @ 30 fps max 1280 x 1024 @ 15 fps max 1600 x 1200 @ 15 fps max 45Lux Frame rate: 640 x 480 @ 4 fps max 1280 x 1024 @ 4 fps max 1600 x 1200 @ 4fps max
Video Format	YUY2, MJPG
OS Support	Windows XP/7
Dimensions	130 x 35 x 40 mm
Operating Temperature	0 ~ 40° C

Packing List

P/N	Description
206KUTCS01	CD-ROM (Manual/ Driver/ Utilities)
1993000170S001	Cable clamp x 2
UTC-P01-A0E	2.M Camera module for UTC-500

Ordering Information

P/N	Description
UTC-P01-A0E	2.M camera module for UTC-500 series

UTC-P02

Magnetic Stripe Card Reader for UTC-500 Series



Specifications

Interface	USB (Cable Length:50cm)
Track Configuration	TRACK 1 / IATA / 210 bpi / 79 Alphanumeric Characters TRACK 2 / ABA / 75 bpi / 40 Numeric Characters TRACK 3 / Thrift / 210 bpi / 107 Numeric Characters
Card Standard	ANSI, ISO, and ABA.
Read Speed	3 ips to 60 ips (7 cm/s to 152 cm/s)
Magnetic Head Life	1,000,000 times (ISO test standard)
OS Support	Windows 98/ME/2000/XP / Win 7
Dimensions	130 x 35 x 40 mm
Operating Temperature	0 ~ 40° C

Packing List

P/N	Description
206KUTCS01	CD-ROM (Manual/ Driver/ Utilities)
1993000170S001	Cable clamp x 2
UTC-P02-A0E	Magnetic stripe Card reader for UTC-500

Ordering Information

P/N	Description
UTC-P02-A0E	Magnetic stripe reader For UTC-500