



Low Loss Reverse SMA to N-Type Cable TEW-L202/L208 (V2.0R)

The low loss Reverse SMA to N-Type Cable extends your wireless Antenna up to 2 or 8 meters to provide optimal placement for your antenna outdoors. Connect business networks from building to building wirelessly or provide wireless Internet access for hot spot applications! This cable makes wireless communication possible by providing low loss communication between your access point and antenna.

FEATURES

- Wi-Fi Compliant with 2.4GHz 802.11 b/g & 5GHz 802.11a Devices for extending wireless networks
- Reverse SMA Female to N-Type Male Connector
- Optimal placement of your existing Wi-Fi Device permits you to maximize its wireless performance
- Flexible outer conductor allows the tightest bend radius available for any cable of similar size and performance
- Provides flexible Low-loss communication for wireless antenna
- Multi-ply bonded outer foil conductor is rated conservatively at > 90 dB
- Weatherproof cable design for outdoors exposure with best materials for UV resistance
- Polyethylene jacketed cable designed for outdoor use
- Easy and quick deployment into a WLAN environment

Low Loss Reverse SMA to N-Type Cable

TEW-L202/L208

SPECIFICATIONS

Construction

Inner Conductor (Solid BC)	• 0.037 in. (0.94 mm)
Dielectric (Foam PE)	• 0.110 in. (2.79 mm)
Outer Conductor (Aluminum Tape)	• 0.116 in. (2.95 mm)
Over Braid (Tinned Copper)	• 0.139 in. (3.53 mm)
Jacket (PE)	• 0.195 in. (4.95 mm)

Mechanical

Bend Radius: Installation	• 0.5 in. (12.7 mm)
Bend Radius: Repeated	• 2.0 in. (50.8 mm)
Bending Moment	• 0.2 ft-lb (0.27 N-m)
Weight	• 0.021 lb/ft (0.03 kg/m)
Tensile Strength	• 40 lb (18.2 kg)
Flat Plate Crush	• 15 lb/in. (0.27 kg/mm)

Environment

Temperature	• Operating: -40° C ~ 85° C (-40°F~185°F) • Storage: -70° C ~ 85° C (-94°F~185°F)
-------------	---

Weight

TEW-L202	• 115g (0.25lb)
TEW-L208	• 340g (0.75lb)


Electrical

Cut-off Frequency	• 41 Ghz
Velocity of Propagation	• 80%
Dielectric Constant	• 1.56
Time Delay	• 1.27 nS/ft (4.17 nS/m)
Impedance	• 50 ohms
Capacitance	• 24.5 pF/ft (80.3 pF/m)
Inductance	• 0.064uH/ft (0.21 uH/m)
Shielding Effectiveness	• > 90 dB
DC Resistance	• Inner Conductor: 7.6 ohms/1000ft (24.9 ohms/km) • Outer Conductor: 4.9 ohms/1000ft (16.1 ohms/km)
Voltage Withstand	• 1000 Volts DC
Jacket Spark	• 3000 Volts RMS
Peak Power	• 2.5 kW

Low Loss Reverse SMA to N-Type Cable

TEW-L202/L208

ANTENNA CABLE SOLUTION



PACKAGE CONTENTS

- TEW-L202 / TEW-L2068
- Weatherproof Tape
- Quick Installation Guide

RELATED PRODUCTS

TEW-AO080	8dBi Outdoor Omni-Directional Antenna
TEW-ASAK	Outdoor Arrestor Kit
TEW-L406/TEW-L412	LMR400 N-Type Male to N-Type Female Cable

ORDERING INFORMATION

TRENDnet®

20675 Manhattan Place, Torrance, CA 90501 USA

Tel: 1-310-961-5500

Fax: 1-310-961-5511

Web: www.trendnet.com

Email: sales@trendnet.com

To Order Please Call:

1-888-326-6061