



Identification	Part No.	Drawing	Dimensions in mm
Fibre optic cable, double ended, single mode Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 58 211 0010 002 33 58 211 0050 002 33 58 211 0100 002 33 58 211 0200 002 33 58 211 0400 002 33 58 211 0500 002 33 58 211 1000 002	double ended a = length	
Fibre optic cable, single ended, single mode Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 58 111 0010 002 33 58 111 0050 002 33 58 111 0100 002 33 58 111 0200 002 33 58 111 0400 002 33 58 111 0500 002 33 58 111 1000 002	Protection level: IP 65 / IP 67 single ended a = length	
Fibre optic breakout cable, single mode Length: 10 m Length: 20 m Length: 100 m	33 58 751 0100 002 33 58 751 0200 002 33 58 751 1000 002	PUR jacket 2-fibre single mode Outer diameter: 6.5 mm Min. bending radius: 10.4 cm Installation: 5.2 cm Operating:	