


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED AND CANCEL	10/11/00
	7156, 6805	



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6835	5.0	.060	.050	0.63	100,000	C-8
7135	5.0	.075	.090	1.13	25,000	C-8
7155	5.0	.115	.150	1.89	40,000	C-8

METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION TITLE T- 3/4 STANDARD AXIAL LEAD LAMP			
	TOLERANCE UNLESS OTHERWISE SPECIFIED					
	1 PL +/- 0.2					
	2 PL +/- 0.20					
	ANGLE +/- 0					
DRAWN BY	APP'VD BY	DATE	SIZE	FSCM NO.	DRAWING NO.	
L. WENGSTROM	Q.C.	10/11/00	A	55335	AXIAL STANDARD T-3/4	
- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.
MANUAL REVISIONS NOT PERMITTED			NONE	10/11/00		
						SHEET 1 OF 1