


(1,27 mm) .050"

**FLE SERIES**

COST EFFECTIVE RELIABLE SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FLE

Insulator Material:

Black Liquid
Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Au over 50µ" (1,27 µm) Ni

Current Rating:

2 A per pin

(6 adjacent pins powered)

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

15mΩ

Insertion Depth:

(1,83 mm) .072" to

(4,37 mm) .172" or

pass-through

Insertion Force:

(Single contact only)

1.5 oz (0,42 N)

Normal Force:

100 grams (0,98 N)

Withdrawal Force:

(Single contact only)

1.5 oz (0,42 N)

Max Cycles:

100+

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max

Mates with:
FTSH, FTS, FW,
FFMD, FMTP




Tiger Beam™
contact

Ideal for
pass-through
applications

Surface
Mount

(1,27 mm) .050"
micro pitch

Available with optional
Pick & Place pads



-A

= Alignment Pin
(Metal or plastic at
Samtec discretion)
(3 positions minimum)

-K

= (4,25 mm) .167" DIA
Polyimide film
Pick & Place Pad
(5 positions minimum)

-P

= Metal Pick &
Place Pad
(5 positions minimum)

-TR

= Tape & Reel

RECOGNITIONS

For complete scope
of recognitions see
www.samtec.com/quality




FILE NO. E111594

FILE NO. 090671_0_000

ALSO AVAILABLE (MOQ Required)

- Other platings
Contact Samtec.

Note: Some lengths, styles
and options are non-standard,
non-returnable.



TAPE & REEL AVAILABILITY

No tooling charges.
Minimum order is the lesser of
a full reel quantity or 125 pieces.
Order any quantity above minimum.
In-house design, manufacture.
Quick turn-around.

Call Samtec for specifications
and ordering information.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685