


REV.	DATE	DESCRIPTION
NC	07/15/03	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	07/15/03										
6						CHECKED												
5						ISSUED			PART DESCRIPTION									
4						SHEET	1 OF 1		SMC P.C. MOUNT JACK									
3	CONTACT PIN	BRASS	GOLD	1						PART NO.								
2	INSULATOR	TEFLON	NATURAL	1						152119								
1	BODY	BRASS	NICKEL	1														
DESCRIPTION						MATERIAL	FINISH	QTY	CAD FILE		DWG. NO.		REV.	NC	SIZE	A	SCALE	NA
									C:/152/152119.DWG		152119.DWG							