



P.C.B. LAYOUT



xx	Pole	A
01	1	3.48
02	2	6.02
03	3	8.56
04	4	11.10
05	5	13.64
06	6	16.18
07	7	18.72
08	8	21.26
09	9	23.80
10	10	26.34
12	12	31.42

Specifications:

Contact rating:	25mA, 24V DC; 100mA, 6V DC min.: 0.1mA, 3V DC
Contact resistance:	50mOhm max.
Insulation resistance:	100MOhm min. at 500V DC
Dielectric strength:	500V, 50Hz for the duration of 1 minute
Operating temperature:	-40°C to +85°C
Mechanical life:	min. 2 000 cycles
Material:	PPS meets UL94V-0
Contacts:	gold plated over nickel
Mounting:	on pc-board
Slide position:	off
Soldering conditions:	auto-soldering: max. 260°C, 5sec.
Vibration:	MIL-STD 202F, method 201A
Shock:	MIL-STD 202F, method 213B, condition A
Sealing:	by protective tape, washable by aqueous detergents and isopropyl alcohol



Tolerances:			Date	Name	DBS 10xx	
			02/07	dr		
DBS 1001 added	02/14	dr			30 10 61	
Revised	10/13	dr				
Vibration / shock	06/10	dr				
Specifications	03/09	dr				
Modifications	Date	Name				Page
						1/1

knitter-switch