

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


B1

REVISED PER ECO-11-005294




30APR11

RK

HMR



SQUARE NUT



MATERIALS AND FINISH

HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
TERMINAL : PHOSPHOR BRONZE, TIN PLATED

2


CONNECTOR ASSEMBLY INCLUDED 2 SQUARE NUTS
LOADED IN CAVITY

3

SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS




NOT CUMULATIVE TOLERANCE



284519-3 AS SHOWN

RECOMMENDED PC BOARD LAYOUT



83.82	23	2-284519-3
80.01	22	2-284519-2
76.20	21	2-284519-1
72.39	20	2-284519-0
68.58	19	1-284519-9
64.77	18	1-284519-8
60.96	17	1-284519-7
57.15	16	1-284519-6
53.34	15	1-284519-5
49.53	14	1-284519-4
45.72	13	1-284519-3
41.91	12	1-284519-2
38.10	11	1-284519-1
34.29	10	1-284519-0
30.48	9	284519-9
26.67	8	284519-8
22.86	7	284519-7
19.05	6	284519-6
15.24	5	284519-5
11.43	4	284519-4
7.62	3	284519-3
3.81	2	284519-2
DIM A	NO OF POS	PART NUMBER

DIMENSIONS:		DWN	07FEB2002
mm		CHK	E. ZANOLINI
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	E. ZANOLINI
0 PLC ±-		PRODUCT SPEC	108-20166
1 PLC ±.3		APPLICATION SPEC	114-20079
2 PLC ±.25		WEIGHT	-
3 PLC ±-		CUSTOMER DRAWING	
4 PLC ±-		SCALE 3:1	
ANGLES ±2		SHEET 1 OF 1	
FINISH		REV B1	



TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
STRAIGHT, 3.81mm PITCH
WITH THREADED FLANGE

SIZE A3 CAGE CODE 00779 DRAWING NO C-284519 RESTRICTED TO -