

MINIATURE LAMP (7371) Details



| Part #              | 7371                        |                       |       |                        |            |
|---------------------|-----------------------------|-----------------------|-------|------------------------|------------|
| Description         | T1 3/4 BIPIN 12V .04A .12CP |                       |       |                        |            |
| Bulb Shape          | T-1 3/4                     | Filament              | C-2F  | Base Style             | G-4 Bi-Pin |
| Glass Diameter (in) | 0.22                        | MOL <sup>†</sup> (in) | 0.63  | LCL <sup>††</sup> (in) | 0.50       |
| Glass Diameter (mm) | 5.5                         | MOL (mm)              | 16.00 | LCL (mm)               | 12.70      |
| Volts               | 12                          | MSCP <sup>‡</sup>     | 0.12  | Avg Life Hrs           | 20000      |
| Watts               | 0.48                        | Amps                  | 0.04  | RoHS Compliant         |            |

**† MOL (Maximum Overall Length):**  
The overall length of a lamp, from the top of the shell to the bottom of the base.

**‡ MSCP (Mean Spherical Candlepower):**  
Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

**†† LCL (Light Center Length):**  
The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.