

Search Results

Evaluate

- FAQ's

Design a Solution

- Specification Sheets
- PDF-TX6500 Cable ..
- PDF-TX6500 Categ ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor


Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'PUP6504VL-UY'

Your search criteria matched only one product, shown below

PUP6504VL-UY



- Exceeds requirements of ANSI/TIA-568-C.2 Category 6 and ISO 11801 2nd Edition Class E channel standards
- Exceeds requirements of ANSI/TIA-568-C.2 and IEC 61156-5 Category 6 component standards
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Reduced attenuation maximizes the amount of signal that reaches the receiver, increasing bandwidth
- Third party tested to comply with ANSI/TIA/EIA-568-B.2-1
- Cable diameter: 0.264 in. (6.7mm) nominal
- Installation temperature range: 32°F to 122°F (0°C to 50°C)
- Operating temperature range: 14°F to 140°F (-10°C to 60°C)
- Channel characterized to 600 MHz, 350 MHz beyond the standard
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap

- Cable supplied in an EZBrake™ reel-in-a-box
- **Available in North America only**

• Part Number	PUP6504VL-UY
• RoHS Compliancy Status	Compliant
• Note	PUP6504VL-UY replaces PUP6504VL-U
• Part Description	Enhanced Category 6, plenum (CMP), 4-pair, UTP copper cable. Copper conductors are 23 AWG construction with FEP insulation. Conductors are twisted in pairs, separated by an integrated pair divider and protected by a low smoke, flame-retardant PVC jacket.
• Product Type	Copper cable
• Color	Violet
• Length (ft.)	1,000
• Cable Color	Violet
• Cable Type	UTP
• CE Compliant	No
• Flammability Rating	CMP
• Jacket Material	Low smoke, flame-retardant PVC
• No. of Pairs	4
• Performance Level	Enhanced Category 6/Class E
• Pricing Description	Copper Cable, Enhanced Cat 6, 4-PR, 23 AWG, UTP, CMP, Violet, 1000 Feet/305m
• Min. Order UOM	FT
• Min. Order Qty.	9000
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.