





1 FINISH: SOLDER TAILS TIN PLATE 0.0051 [0.000200] MIN. THICK. CONTACT AREA 0.00076 [0.000030] MIN. HARD GOLD OVER 0.00127-0.00254 [0.000050-.000100] LOW STRESS NICKEL.

2 CHARACTERS 2.5 [0.10] HIGH, COLOR BLACK.



P.C. BOARD HOLE LAYOUT
SWITCH SIDE

SUPERSEDED BY 1-435167-1

		SWITCH POSITION															
		0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
COMMON TO	1		●		●		●		●		●		●		●		●
	2			●	●			●	●			●	●			●	●
	4					●	●	●	●					●	●	●	●
	8									●	●	●	●	●	●	●	●

435167-1

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
CASE: THERMOPLASTIC, COLOR
NATURAL
CONTACT: BERYLLIUM COPPER

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.5 [0.02]
3 PLC ±-
4 PLC ±-
ANGLES ±0°30'

FINISH
1

DWN
R. TALLEY
8-7-91

CHK
R. MILLER
8-7-91

APVD
D. HUFFMAN
8-7-91

PRODUCT SPEC
108-7514

APPLICATION SPEC
114-7005

WEIGHT
-

CUSTOMER DRAWING

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
ROTARY SWITCH ASSY,
16 POSN, 6000 SERIES
HEXADECIMAL

SIZE
A3

CAGE CODE
00779


DRAWING NO
C- 435167

RESTRICTED TO
-


SCALE
2:1

SHEET
1 OF 4

REV
L



- 1 FINISH: SOLDER TAILS TIN PLATE 0.0051 [.000200] MIN. THICK. CONTACT AREA 0.00076 [.000030] MIN. HARD GOLD OVER 0.00127-0.00254 [.000050-.000100] LOW STRESS NICKEL.
- 2 CHARACTERS 2.5 [.10] HIGH, COLOR BLACK.




P.C. BOARD HOLE LAYOUT
SWITCH SIDE

		SWITCH POSITION															
		0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
COMMON TO	1		●		●		●		●		●		●		●		●
	2			●	●			●	●			●	●			●	●
	4					●	●	●	●					●	●	●	●
	8									●	●	●	●	●	●	●	●

1-435167-1
PART NO


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 8-7-91	AMP AMP Incorporated Harrisburg, PA 17105-3608			
		CHK R. MILLER 8-7-91				
DIMENSIONS: mm [INCHES]		APVD D. HUFFMAN 8-9-91	NAME ROTARY SWITCH ASSY, 16 POSN, 6000 SERIES HEXADECIMAL			
		PRODUCT SPEC 108-7514	SIZE A3		CAGE CODE 00779	DRAWING NO C- 435167
		APPLICATION SPEC 114-7005	RESTRICTED TO -		SCALE 2:1	
MATERIAL CASE: THERMOPLASTIC, COLOR NATURAL CONTACT: BERYLLIUM COPPER		WEIGHT -	CUSTOMER DRAWING		SHEET 2 OF 4	REV L
FINISH 1						



1 MATERIAL; CASE-THERMOPLASTIC, COLOR NATURAL.
WHEEL-THERMOPLASTIC, COLOR BLACK.
CONTACT-BERYLLIUM COPPER.


△2 FINISH: SOLDER TAILS TIN PLATE 0.0051 [.000200]
MIN. THICK. CONTACT AREA 0.00076 [.000030]
MIN. HARD GOLD OVER 0.00127-0.00254
[.000050-.000100] LOW STRESS NICKEL.

3 CHARACTERS 2.3 [.09] HIGH, COLOR WHITE.



P.C. BOARD HOLE LAYOUT
SWITCH SIDE

		SWITCH POSITION															
		0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
COMMON TO	1		●		●		●		●		●		●		●		●
	2			●	●			●	●			●	●			●	●
	4					●	●	●	●					●	●	●	●
	8									●	●	●	●	●	●	●	●

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY	8-7-91	 AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK R. MILLER	8-7-91		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. HUFFMAN	8-9-91	NAME	
0 PLC ±- 1 PLC ±- 2 PLC ±0.5 [0.02] 3 PLC ±- 4 PLC ±- ANGLES ±0°30'		PRODUCT SPEC 108-7514		ROTARY SWITCH ASSY, 16 POSN, 6000 SERIES HEXADECIMAL	
		APPLICATION SPEC 114-7005		SIZE	RESTRICTED TO
MATERIAL		WEIGHT		CAGE CODE	DRAWING NO
		-		A3 00779	C- 435167
FINISH		CUSTOMER DRAWING		SCALE	SHEET
				2:1	3 OF 4
				REV	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

FT

	DIST
--	------

69

REVISIONS

	F
--	---

LTR

DESCRIPTION



DATE _____

DWN

APVD


[illegible]

SEE SHEET 1



△ 2 FINISH: SOLDER TAILS TIN PLATE 0.0051 [0.000200]
MIN. THICK. CONTACT AREA 0.00076 [0.000030]
MIN. HARD GOLD OVER 0.00127-0.00254
[0.000050-.000100] LOW STRESS NICKEL.


3 CHARACTERS 2.3 [.09] HIGH, COLOR WHITE.



P.C. BOARD HOLE LAYOUT
SWITCH SIDE

SUPERSEDED BY 2-435167-1

		SWITCH POSITION															
		0	1	2	3	4	5	6	7	8	9	A	B	C	D	E	F
COMMON TO	1		●		●		●		●		●		●		●		●
	2			●	●			●	●			●	●			●	●
	4					●	●	●	●					●	●	●	●
	8									●	●	●	●	●	●	●	●

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY		8-7-91		AMP		AMP Incorporated					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. MILLER		8-7-91		Harrisburg, PA 17105-3608					
		APVD D. HUFFMAN		8-9-91		NAME ROTARY SWITCH ASSY, 16 POSN, 6000 SERIES HEXADECIMAL							
		PRODUCT SPEC 108-7514											
		APPLICATION SPEC 114-7005		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		WEIGHT -		A3		00779		C- 435167		-			
MATERIAL		FINISH		CUSTOMER DRAWING				SCALE 2:1		SHEET 4 OF 4		REV	
													