

In most applications, a signal booster ([B120-000-SL](#)) should be used with this cable to ensure a signal strong enough for your display. An alternate, more cost effective solution is to use a Tripp Lite DVI over Cat5 Extender ([B140-101X](#)) in place of a 100 ft. DVI cable and signal booster.

## DVI High Definition Single Link Digital TMDS Monitor Cable (DVI-D M/M), 100-ft.

MODEL NUMBER: **P561-100-HD**



### Highlights

- 24AWG High Definition Cable
- For use with Single TMDS Link specified video cards
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

### System Requirements

- DVI monitor and computer

### Package Includes

- 100-ft. DVI High Definition Single Link TMDS Cable (DVI-D M/M)

### Description

Tripp Lite's 100 ft, High Definition DVI Single Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. 24AWG wire and gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display.

### Features

- 24AWG High Definition Cable
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signalling for transmission speeds to 9.9Gbps
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projector
- In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display.

## Specifications

General Info	
Product Group	DISPLAY & AUDIO CABLES
OVERVIEW	

Intended Application	Connecting Peripherals
Cable Type	DVI
Model Type	DVI
<b>INPUT</b>	
Cable Length (ft.)	100
Cable Length (m)	30
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332174734
<b>PHYSICAL</b>	
Color	Black
Style	DVI
<b>CONNECTIONS</b>	
Connector A	DVI-D SINGLE LINK (MALE)
Connector B	DVI-D SINGLE LINK (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.