

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	10A 125VAC, 6A 250VAC 1/2HP 125/250VAC	
Configured For	12VDC 14V	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temp.	- 25 °C ~ 85 °C	
Function	4P SPST ON-OFF LED Independent	
Lamp Type	LED 12VDC 14V w/resistor	

MATERIAL:

Frame: Black, Nylon 66 (94-V2)

Actuator: PC Clear (94-V2), For Color Ref. "X" in
Actuator/LED Color Chart and CW P/N.




LED: For Color Ref. "X" in Actuator/LED Color Chart
and CW P/N.

Terminals: Silver plated, Copper alloy

Waterproof Rubber: Black, Silicone


Printed: None

Waterproof: IP65





ACTUATOR/LED COLOR	X
Amber	A
Green	G
Red	R
Blue	U
White	W

RoHS Compliant



Full Travel: 4.5mm



CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 6/28/12

Rev. 0

Unit: mm

Checked By: *G. Guld*

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB527D2L02BX1