



Aluminum Enclosures with Coax Connectors

Die Cast Aluminum Boxes

► Coax Connectors Are 50 Ohm Nominal Impedance
 ► Boxes with Connectors Are Rated at 500 VRMS Max., +150°C (+302°F) Max. Except for Model 2399 Which Is Rated at 335 VRMS Max. and Model 2411 Which Is Rated at 1000 VRMS

Die Cast Aluminum Boxes
 Provide excellent RF/EMI protection when used with the included cover and screws. Available with no finish or blue baked enamel per Federal Standard 595 #295109 over primer wash per DOD-P-15328. Covers are aluminum 1100-H14 with clear anodize finish per MIL-A-8625. All boxes are supplied with covers and cover screws.

Materials: Miniature, Size A, B, C, D, E, J and L — Die cast alloy A380 or A384; Size F, G, H and I — Extruded aluminum, alloy 6063-T5 or equivalent.

Stock No.	Mr.'s Type	Box Size	Finish	Each
885-3753	3753	Miniature	Blue Baked Enamel	6.40
885-3754	3754	Miniature	None	6.15
885-2397	2397	A	Blue Baked Enamel	6.40
885-2400	2400	A	None	5.90
885-0550	2417	B	Blue Baked Enamel	6.60
885-2428	2428	B	None	6.25
885-3601	3601	D	Blue Baked Enamel	11.70
885-3606	3606	D	None	11.40
885-0665	2901	C	Blue Baked Enamel	16.25
885-2906	2906	C	None	13.75
885-4227	4226	E	Blue Baked Enamel	42.00
885-5186	5186	E	None	39.20
885-6016	4655	J	Blue Baked Enamel	20.10
885-6015	5255	J	None	18.10
885-4903	4903	L	Blue Baked Enamel	24.10
885-5203	5203	L	None	23.60
885-3301	3301	F	Blue Baked Enamel	25.30
885-3306	3306	F	None	23.20
885-0001	3311	G	Blue Baked Enamel	30.20
885-3316	3316	G	None	28.60
885-3742	3742	H	Blue Baked Enamel	37.25
885-4641	4641	I	Blue Baked Enamel	70.00

Miniature Size Box, BNC Female Each End
 1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
 885-3751. Model 3751 EACH 24.70

Size B Box, BNC Female "T"
 1st End: BNC female with solder turret terminal screws. Center: Same as first end.
 885-3232. Model 3232 EACH 32.25

Size A Box, Isolated BNC Female Each End
 Blue baked enamel. Connectors: BNC male/female.
 885-3752. Model 3752 EACH 23.40

Size A Box, BNC Female Box
 Blue baked enamel. Connectors: Model 2390 — BNC female/female; Model 2391 — BNC male/female.
 885-2390. Model 2390 EACH 20.35
 885-0525. Model 2391 EACH 22.95

Size A Box, BNC Female "T"
 1st End: BNC female with solder turret terminal screws. Center: Same as first end.
 885-2392. Model 2392 EACH 31.20

Size A Box, "T" Two BNC Females to BNC Male
 1st End: BNC male with solder turret terminal screws. Center: BNC female with solder turret terminal screws. 2nd End: Same as center.
 885-2401. Model 2401 EACH 33.45

Size A Box, SMA Female Each End
 1st End: SMA female with solder turret terminal screws. Gold plated per requirements of MIL-C-39012. 2nd End: Same as first end.
 885-2399. Model 2399 EACH 50.00

Size A Box, BNC Female Each End
 1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
 885-3230. Model 3230 EACH 20.15

Size B Box, BNC Female to BNC Male
 1st End: BNC male with solder turret terminal screws. 2nd End: BNC female with solder turret terminal screws.
 885-2398. Model 2398 EACH 43.45

Size B Box, BNC Female Each End
 1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
 885-2902. Model 2902 EACH 32.35

Size D Box, BNC Female Each End
 1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
 885-3602. Model 3602 EACH 26.85

Size D Box, BNC Female to BNC Male
 1st End: BNC female with solder turret terminal screws. 2nd End: BNC male with solder turret terminal screws.
 885-3603. Model 3603 EACH 31.10

Size C Box, BNC Female Each End
 1st End: BNC female with solder turret terminal screws. 2nd End: Same as first end.
 885-2902. Model 2902 EACH 32.35

Size J Box, Five BNC Females
 1st End: Four BNC females. 2nd End: BNC female with solder turret terminal screws.
 885-4656. Model 4656 EACH 47.00

Size F Box, BNC Female Each End
 1st End: BNC female with solder turret screws. 2nd End: Same as first end.
 885-3231. Model 3231 EACH 43.00

Phenolic Boxes

Phenolic Box, 2.25" x 1" x 1"

Housing: Phenolic, black. Cover: XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. Rating: +150°C (+302°F) max. 885-2103. Model 2103 EACH 4.42

Component Mounting Box, Double Banana Jack to Double Banana Plug, 2.38" x 1.53" x 1.53"

1st End: Double banana jack. Brass, bright tin plated. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. Rating: 5000 VDC, 15 amps, +150°C (+302°F) max. 885-2224. Model 2224 EACH 12.50

Phenolic Box, 2.38" x 1.53" x 1.53"

Housing: Phenolic, black. Cover: XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. Rating: +150°C (+302°F) max. 885-2104. Model 2104 EACH 4.25

Component Mounting Box, Double Banana Jack to Double Banana Plug, 1.75" x 1.44" x 0.69"

1st End: Double banana jack. Brass, bright tin plated. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. Rating: 5000 VDC, 15 amps, +150°C (+302°F) max. 885-2098. Model 2098 EACH 12.15

Phenolic Box, 1.75" x 1.44" x 0.69"

Housing: Phenolic, black. Cover: XP laminated paper base phenolic, black. Includes 2 #2-56 cover screws. Rating: +150°C (+302°F) max. 885-2105. Model 2105 EACH 4.25

Component Mounting Box, Binding Posts to Double Banana Plug, 1.75" x 1.44" x 0.69"

1st End: Double binding post. Brass, bright tin plated. Accepts standard banana plugs. Polycarbonate insulation. One black and one red. 2nd End: Double banana plug. Brass body, beryllium copper spring, nickel plated. Supplied with cover and cover screws. Rating: 2500 VDC, 15 amps, +115°C (+239°F) max. 885-2259. Model 2259 EACH 15.15

Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com

ALLIED ► 67