

4

3


2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
F	00		B	HOLE DIA. TOLERANCES	09JUN2006	JJD	YP
			C	ECR 07-025006	29OCT2007	JT	GR

D


COUPE C - C



STAMP : AMP 12-10*

BODY 0.98±0.05 TONGUE THICKNESS

Ø8.34±0.13 FOR 5/16 OR M8 STUD



FOR INSULATION
Ø2.60 - 5.44
Ø7.40 MAX

SLEEVE

INSULATION

SERRATIONS

13.49±0.15

0.79 MIN

11.56 MIN

27.69 MAX

34.50MAX

WIRE TERMINAL	1577649-1	BODY : COPPER ANNEALED FINISH : NICKEL PLATED
		SLEEVE : COPPER ANNEALED FINISH : NICKEL PLATED
		INSULATION : PEEK COLOR : BLACK
DESCRIPTION	PART NUMBER	MATERIAL & FINISH

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN JJ. DESPRETZ 27FEB2006	tyco Electronics Tyco Electronics France SAS 95300 Pontoise, France		
DIMENSIONS: mm		CHK G-ROBERT 27FEB2006			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Y-PETRONIN 27FEB2006	NAME TERMINAL, PEEK PIDG STRATO, 10 AWG		
		PRODUCT SPEC 108-15356			
		APPLICATION SPEC 114-15102	SIZE A3	CAGE CODE 00779	DRAWING NO C-1577649
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT 2,9 gr	RESTRICTED TO -		
CUSTOMER DRAWING		SCALE 5:1	SHEET 1	OF 1	REV C