




REV. C  
DCO 300855

TOLERANCES  $\pm .010"$  - UNLESS  
OTHERWISE SPECIFIED

COIL: @ 25°C  
 RESISTANCE 320 OHMS  $\pm 10\%$   
 NOMINAL VOLTAGE 28 VDC  
 MUST OPERATE 13.5 VDC MAX.  
 TRANSIENT SUPPRESSION - 42 VDC MAX.  
 MUST RELEASE 5.5 VDC MAX., 2.3 VDC MIN.


ENVIRONMENT:  
 VIBRATION 33 Hz TO 3000 Hz @ 30 g's  
 SHOCK 200 g's 6 MS. DURATION  
 TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 10 MS MAX.

CONTACT BOUNCE 1 MS MAX.

CONTACT BREAK BOUNCE 0.1 MS MAX.

## CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:  
 10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE.  
 100,000 OPERATIONS

DR. B.D. 07MAR2008

CK. J.M.B. 5/14/08

**Tyco Electronics**

©COPYRIGHT 2005

TYCO ELECTRONICS CORPORATION  
 ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG ITEM

TE NUMBER  
 9-1617751-9

CII PART NUMBER

FC A-210-C X4