


H48-6A

Thermal Conductive Pad



Features



Very good thermal conductivity
Soft and high compressibility
Natural tack
Easy to assemble
Very good insulator

Applications

Electronic components: IC / CPU / MOS
LED / M/B / P/S / Heat Sink / LCD-TV / Notebook PC / PC / Telecom Device /
Wireless Hub etc....
DDR II Module / DVD Applications / Hand-Set applications etc...



Thermal Resistance V.S Pressure V.S Deflection




Properties


Thermal Conductivity: 4 W/mK
(W/mK - Z Axis)

REACH Compliant
RoHS Compliant

Hardness: 25 (Shore A)
(Shore A)




Testing sample thickness : 1.0 mm



In the thermal resistance vs pressure vs deflection charts H48-6A provides low thermal impedance.
As the pressure increases the thermal impedance decreases. H48-6A provides good compliance and softness.

Property	H48-6A	Unit	Tolerance	Test Method
Colour	Henna	-	-	Visual
Thickness (Available thickness range)	0.3 - 20	mm	-	ASTM D374
	0.0118 - 0.787	inch	-	ASTM D374
Thermal Conductivity	4	W/mK	-	ASTM D5470
Flammability Rating	V-0	-	-	UL 94
Dielectric Breakdown Voltage	>5	kV/mm	-	ASTM D149
Weight Loss	<1	%	-	ASTM E595
Specific Gravity	2.48	g/cm³	±0.2	ASTM D792
Working Temperature	-40 to 200	°C	-	-
Volume Resistance	>10 ¹¹	Ohm-cm	-	ASTM D257
Elongation	120	%	±13	ASTM D412
Tensile Strength	8	Kgf/cm²	±2	ASTM D412
Standard Shape	-	Sheets 320-320mm	-	-
Hardness	25	Shore A	±5	ASTM D2240

Available with an adhesive backing



1. Part Number
2. Size X-Y-Z
3. Adhesive backing - 0=None, 1A=one side, 2A=two sides
4. Quantity