

Trumeter's 7954 and 7957 Multi-function time relays

New Products



Versatile and easy to program

Trumeter's new range of digital time relays offer 8 or 18 operating modes, easily configured on the 3 digit LCD display; a wide timing range of 0.1s - 999Hr to suit all applications; a clear indication of the changeover relay status via the front panel LED; can accept a wide range of operating voltages for most installations. The key lock feature means settings cannot be tampered with, meaning 100% reliable operation.

Features

- Compact 17.5mm DIN rail mountable
- 3 digit LCD for easy programming
- Tamper proof with key lock feature
- Wide timing range: 0.1s - 999Hr
- Multi-function: (8 or 18) non-signal and signal based functions
- Multi-voltage: 24 - 240VAC/VDC
- Option to select up/down counting
- CE, UI & cUI approved

Operating Modes


7957

- ON Delay
- Cyclic OFF/ON
- Cyclic ON/OFF
- Impulse on Energising
- Accumulative Delay on Signal
- Accumulative Delay on Inverted Signal
- Accumulative Impulse on Signal
- Signal ON Delay
- Inverted Signal ON Delay
- Signal OFF Delay
- Impulse ON/OFF
- Signal OFF/ON
- Leading Edge Impulse 1
- Leading Edge Impulse 2
- Trailing Edge Impulse 1
- Trailing Edge Impulse 2
- Delayed Impulse
- Inverted Signal ON Delay (Type 2)

7954

- ON Delay
- Cyclic OFF/ON
- Cyclic ON/OFF
- Signal ON/OFF
- Signal OFF Delay
- Interval
- Signal OFF/ON
- One Shot Output

MOUNTING DIMENSIONS (mm)



Ordering Information

- 7954 Multi-Function Digital Timer, 8 Functions, 1 C/O, 24 - 240VAC/DC
7957 Multi-Function Digital Timer, 18 Functions, 1 C/O, 24 - 240VAC/DC