


Model 3784 Minigrabber® Test Clip To Stacking Miniature Banana Plug



FEATURES:

- Provides a Minigrabber output from a miniature Banana Jack.
- Mates to Model #2192 or any miniature Banana Jack.
- Miniature Banana plug is vertically stackable.

MATERIALS:

Conn: 1st end - Minigrabber®

Material: Contact - Beryllium Copper

Spring – Stainless steel

Finish: Contact – Gold plated

Insulation: Glass filled nylon. Color matches color of wire.

Marking: “MINIGRABBER® “POMONA ELECTRONICS.”

Wire: 20 AWG, stranding 41 x 36 t.c., PVC insulated, 2.21 (.087) O.D.

Color: See Ordering Information

Marking: “POMONA 3784-*. ”

Conn: 2nd end – Miniature Banana Plug

Material: Spring - Beryllium Copper

Plug Body – Brass

Finish: Gold plated over electroless nickel

Insulation: Polypropylene molded to plug body and wire.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max

Operating Voltage: 300 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 3784-XX-*

XX = Cable Lengths, Standard Lengths: 12” (305), 24” (610), 36” (914), 48” (1219) & 60” (1524). Additional lengths can be quoted upon request.

*= Color, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Ordering Example: 3784-60-2 Indicates 60” in length, color is Red

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90583 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3784-24-0](#) [3784-24-2](#) [3784-36-0](#) [3784-36-2](#)