

Specifications:

Sound Level Category	Loud
Mode of Operation	Medium Pulse Rate (5pps)
Voltage Rating	48 to 120 VAC/DC
Frequency	2900 Hz $\pm$ 500 Hz
Loudness @ 2 FT	85 to 95 dB(A) typ.
Current Draw	40 mA Max
Housing Material	Nylon 6/6 (Color: Black)
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Panel Mounting	Recommended hole size is 1.25in (31.75mm). Threaded front will fit standard 30mm (1.181in) hole.
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs
Weight (Typical)	1.5 oz (43 g)
NEMA 3R, 4X, & 12	Approved with use of ACC03.
Options	For other options contact factory

Dimensions: Inches (mm)

RoHS Compliant
