





CAPACITANCE	1500 pF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
DCR	.01 Ω MAX.
WORKING VOLTAGE	85°C 350 VDC 125°C 200 VDC

MIN. IL PER MIL-STD-220, 25°C, NO LOAD

FREQ. (MHz)	dB
10	5
100	40
1GHz	60
10GHz	60

SCHEMATIC



MARKING:

PART : 89001
BAG : 1289-001
DATE CODE
QTY./BAG (200 MAX.)

	08	7	6	5	4	3	2	1	0	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api technologies corp. FAIRVIEW PENNSYLVANIA	
	CN 64826-ENG	CN 207435	CN 202979	CN 180696	CN 170043	CN 150202	CN 149285	CN 148903	CN 146113	CHANGE NOTICE	Fractions ± 1/64	Dwn. J.KAUFFMAN	Description
											Dec. .xx±		
											Dec. .xxx± .010	Ckd. 7-24-12	FILTER
											Angles ±0° 30'		
											CODE IDENT. NO. DLSP2	Apvd.	1289-001
Scale NONE													