



EMPTY ENCLOSURE

AKL 2-g



AKL 2-g

Empty enclosure

300 x 300 x 132 mm
Article number: 74040201

Empty enclosure, with attachment bushes, sealing and insulating plugs, base and cover: polystyrene, grey similar to RAL 7035



Technical data

Measures

Width:	300 mm
Length:	300 mm
Height:	132 mm
Inner height:	114 mm

Material

Base:	Polystyrene, grey, similar to RAL 7035
Cover:	Polystyrene, grey, similar to RAL 7035
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced

Other attributes

Ingress protection:	IP65 - acc. EN
---------------------	----------------

Accessory

AK MPI 2
AK NS35-250
NS35-216/3
AK ABL-ES
ASS-gro
AK ABF 2
AK TW



EMPTY ENCLOSURE

AKL 2-g

60529 / DIN VDE
0470-1

Impact resistance:	IK07 acc. DIN EN 5012 / VDE 0470 Part 100
--------------------	---

Rated insulation voltage AC:	690 V V
------------------------------	---------

Rated insulation voltage DC:	1000 V
------------------------------	--------

PVC-free:	Yes
-----------	-----

Heavy metals-free:	Yes
--------------------	-----

Silicone-free:	Yes
----------------	-----

Combustion behaviour to UL:	HB acc. UL94
-----------------------------	--------------

Combustion behaviour to VDE:	650°C acc. VDE 0471/ EN 60695
------------------------------	----------------------------------

Knockouts:	Yes
------------	-----

sealable:	Yes
-----------	-----

Environmental attributes

Ambient temperature (min.):	-25 °C
-----------------------------	--------

Ambient temperature (max.):	40 °C
-----------------------------	-------

Ambient temperature (24 h):	35 °C
-----------------------------	-------

Max. rel. humidity at 25° C (short Therm):	95%
---	-----

Max. rel. humidity at 40° C:	50%
------------------------------	-----