

Diagonal cutter - MICROFOX-S ESD - 1212480

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



ESD electronic diagonal cutter, round head, without chamfer, with opening spring, non-reflective coating and phosphate-treated, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1 mm diameter

Why buy this product

- ✓ Ergonomically designed two-component handles for fatigue-proof and non-slip use
- ✓ Opening spring for uniform, smooth opening
- ✓ Made from special high-grade tool steel
- ✓ Screwed precision-joint for permanent stability and optimum results
- ✓ Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- ✓ The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5

Key commercial data

Packing unit	0
Minimum order quantity	1
Catalog page	Page 260 (CL2-2011)
GTIN	 4 046356 527125
Custom tariff number	82032000
Country of origin	GERMANY

Technical data

General

Length (b)	110 mm
Weight	70 g

Classifications

eclass

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301

Diagonal cutter - MICROFOX-S ESD - 1212480

Classifications

eclass

eCl@ss 6.0	21043706
eCl@ss 7.0	21043706

etim

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000165

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--