


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C MIN	M $\pm .03$	H $\pm .01$
PV18-5SLF	#5	.82 (20.83)	.26 (6.60)	.19 (4.83)	.70 (17.78)	.13 (3.30)
PV18-6SLF	#6	.82 (20.83)	.27 (6.86)	.19 (4.83)	.70 (17.78)	.14 (3.56)
PV18-8SLF	#8	.87 (22.10)	.29 (7.37)	.23 (5.84)	.75 (19.05)	.16 (4.06)
PV18-10SLF	#10	.88 (22.35)	.33 (8.38)	.23 (5.84)	.74 (18.80)	.19 (4.83)



NOTES:

- CSA CERTIFIED FOR:
 - 600 V MAX. VOLTAGE RATING
 - 221°F (105°C) MAX. TEMP. RATING
 - #22-18 AWG STRANDED COPPER WIRE
- PACKAGE QTY.: STD C=100
BULK M=1000
- MATERIAL:
 - STAMPING - .032 (.81) THK COPPER, TIN PLATED
 - HOUSING - RED VINYL
- WIRE STRIP LENGTH: $5/16 \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ (7.9 $\begin{smallmatrix} +.8 \\ -.0 \end{smallmatrix}$)
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
 - CSA APPROVED: CT-510, CT-1551, CT-1550
 - PANDUIT APPROVED: CT-400



CERTIFIED
LR31212

A41460_04

04	1/01	RM		FILESPEC WAS N41460AA_PCD_03				PANDUIT CORP. TINLEY PARK, ILLINOIS			
03		JKD		ADDED CT-1551 & CT-1550 TOOLS	07632						
02	12/94	TH	RLS	UPDATED NOTES AND DIMENSIONS	02708	LA	TFKE	#22-18 BARREL VINYL INSULATED SHORT LOCKING FORK .150 MAX INSUL DIA			
01	3/91	DL		TANG WIDTH INCREASED PART NO PV18-5SLF, PV18-6SLF	00403	LA	KRS				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	Ck'D	SCALE	DRAWING NO.
								DRL	RLS	NONE	A41460