

3 Outlet, Direct Plug-In, 540 Joules, 2.1 amp USB charger - Protect It! Surge Suppressor

MODEL NUMBER: **SK120USB**



Description

The SK120USB surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability with fold down plug and carrying pouch and features 3 outlets, 1 in front and 1 on each side of unit and 540 joules of surge energy absorption. The diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 3 outlets / direct plug-in - 1 on face of product and 1 on each side
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- Fold down plug
- Carrying pouch
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW

Intended Application	Home/Office
----------------------	-------------

OUTPUT

Frequency compatibility	60 Hz
-------------------------	-------

Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Fold down plug
- Carrying pouch
- Diagnostic LED
- \$5,000 Ultimate Lifetime Insurance (USA & Canada only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection
- Dual port USB charging ports for smartphones, tablets, MP3 players and other portable devices

Package Includes

- SK120USB surge suppressor
- Carrying pouch

Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	3 NEMA 5-15P
Outlet Type	NEMA 5-15P
USB Charging Ports	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input connection type	NEMA 5-15P input plug
Input plug features	120V, 15A
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	540
AC suppression response time	< 1ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping voltage (RMS)	500
AC suppression surge current rating	27,000
UL1449 let through rating	500, 400, 500
Immunity	Conforms to IEE 587/ANSI C62.41
PHYSICAL	
Material of construction	Plastic
Integrated keyhole mounting tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black
Receptacle Color	Black
Style	Direct plug-in
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance
(U.S., Canada & Puerto Rico)

\$5,000 [Ultimate Lifetime Insurance](#)

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SK120USB](#)