




FEATURES:

- Extra large Alligator features a 0.8" (20mm) jaw opening
- Strain reliefs are on clip and plug ends for added pull strength
- Designed to comply with IEC 1010, which is an international safety standard

MATERIALS:

Alligator: Jaw: Nickel steel

Insulation: Polyamide

Wire: 18 AWG, Silicone jacket

Plug: Body: Brass, nickel plated

Spring: Beryllium Copper

RATINGS:

CAT III, 1000V, 20 Amperes

ORDERING INFORMATION: Model 6570-XX-*

XX = Wire Length, Standard Length: 36" (91cm), 60" (152cm)

* = Standard Colors, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90978 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com