


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	B	CHG & ADDED DIMENSIONS		J.C.	2/3/93			J.L.	
948	C	CHG TO TABULAR SPEC		HYD	8/2/00	JC	11/22/00	JC	11/22/00



SPC TYPE NO.	VOLTS	AMPS	WATTS	EFC	FILAMENT	LIFE (HOURS)
10ESB	10	0.035	0.35	450	C-6	1000
12ESB	12	0.04	0.48	650	C-2V	7500
16ESB	16	0.04	0.64	750	C-2F	7500
24CSB	24	0.017	0.408	100	C-2F	15000
24ESB	24	0.04	0.96	850	C-2F	8000
28ESB	28	0.04	1.12	1500	C-2F	6000

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE: T-2 TELEPHONE SLIDE #5 (SHORT)			
	J.C.	2/3/92				
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	J.P.	2/5/93	A	TA-258	TA-258.DWG	C
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES	SHEET: 1 OF 1
	J.L.	2/8/93				