



**Jack**

16PJ225

**KOBI CONN**

**Jack**



**Dimensions: In.**  
(except where noted)

#### **SPECIFICATIONS**

Type:	3.5mm inline mono
Breakdown voltage:	500VAC for 1 minute
Insulation resistance:	100MΩ min. @ 500VDC
Contact resistance:	50mΩ max.
Rated life:	5,000 cycles min.
Contact A:	nickel plated brass
Contact B:	nickel phated phosphor bronze
Cap:	polyethylene
Body:	polyamide
Terminal:	nickel plated brass

Date Last Revised: 4-5-05

**Available from Mouser Electronics**  
**1-800-346-6873**  
**www.mouser.com**

KC-300422

**16PJ225**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[16PJ225](#)