



Sample photo

Order symbol: PCM 175/150 G
Product nbr: 6016323
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074052278
El. number:
 Finland 3435230
 Denmark 8212027543
 Sweden 2535341

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	180	150	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 94 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
inch:		7.1	7.1	5.9	
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		TPE			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 175		Mounting plate			
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate			
HFP 180		Front plate hinge series			
Certificates:					
Germanischer Lloyd (GL)					
Underwriters Laboratories					
Det Norske Veritas					
Fimko					
Europe EN 50298 1998					
UL Canada					
Gost R					

