



19" case, 9 U




Front view



h = case foot height, HE = U, internal usable height



Side view



Usable depth d = D - 24 mm

Part no.: 10225-640

Features:

- Desk-top enclosure (pre-assembled)
- With handle shell
- Steel top cover, base plate and rear panel
- Al die-cast front and rear frames
- Ventilation slots in base plate
- Air vents in rear panel



Technical information:

Height	Height H	h	Depth D	Usable depth d	Width
9 U	420 mm	13 mm	600 mm	576 mm	520 mm

Delivery comprises: kit

Item	Qty	Description
1	1	Front frame, Al die-cast, RAL 7016, with 19" grid
2	1	Rear frame, Al die-cast, RAL 7016, with 19" grid
3	2	Side profile at top, Al extrusion, RAL 7016
4	2	Side profile at bottom, Al extrusion, RAL 7016
5	2	Side panel, St, 1.5 mm, RAL 9006, with GND/earthing tag
6	2	Handle shell, PC, RAL 7016, UL 94 V-0, load-carrying capacity: 60 kg/pair
7	1	Cover plate, St, 1 mm, RAL 9006, with GND/earthing tag
8	1	Base plate, St, 1 mm, RAL 9006, with GND/earthing tag
9	1	Rear panel, St, 1 mm, RAL 9006, with GND/earthing tag
10	4	Case foot with anti-slip protection, PC, black, UL 94 V-0
11	1	Assembly kit