

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301060097](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Assembled Rubber Stringlight 200W 14/3 SOOW 1.52m (5.0') Lead Locking with Guard 3.04m (10.0') Overall Length 30.48m (100.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA L5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Super-Safeway
Type	String Lights
UPC	78678804132
Physical	
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	N/A
Depth	46.48mm (1.830")
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	101.60mm (4.000")
Length	30.48m (100.0')
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Assembled
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	14/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	310243



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130106](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION