


Model 4538 Minigrabber® Test Clip To Stacking Banana Plug With Retractable (Coiled) Cord



FEATURES:

- Retractable cord to allow connections at various lengths.
- Banana Plug stackable vertically and cross stackable.
- Ideal for connecting test equipment to terminals or wire wrap posts.

MATERIALS:

Conn: 1st End - Minigrabber® Test Clip

Material: Contact – Beryllium Copper per QQ-C-533, Alloy 165.

Spring – Stainless steel, Alloy 302.

Finish: Contact – Gold plated per MIL-G-45204, Type I, Class 00.

Insulation: Glass filled nylon. Color matches color of wire.

Retractable Cord: 20 AWG, stranding 42 x 36 t.c., PVC insulated, 3.71 (.146) O.D.

Color: See Ordering Information

Conn: 2nd End – Standard Stacking Banana Plug

Material: Spring - Beryllium Copper per QQ-C-533, Alloy 172, cond. HT.

Plug Body - Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire. Color matches color of wire.

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 4538-*

*= Color, -0 Black, -2 Red

Ordering Example: 4538-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4538-2](#) [4538-0](#)