






ASSEMBLY - VIEW FROM FRONT



ISOMETRIC VIEW




6' FOOT TWIST
POWER CORD
(NEMA L5-20P)

ASSEMBLY - VIEW FROM BOTTOM

ASSEMBLY - VIEW FROM SIDE

1589H6C1BKRF
Finish - Front - Black Painted Steel
Back - Black Painted Steel
Rated - 125 VAC, 60 Hz, 20 Amps
Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Recognized Standard UL1363
Cord Length
1589H6C1BKRF - 6' Foot Twist Power Cord (NEMA L5-20P)
1589H6D1BKRF - 15' Foot Twist Power Cord (NEMA L5-20P)



SECTION A-A

