

**STRADA-DW-GD LENSES FOR OSRAM-OS
DRAGON SERIES OF LEDs**

- Specially designed for Osram-os Golden Dragon Plus LEDs.
- New extremely wide SIDE-EMITTING design with very and uniform light distribution.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions
- Best available optical efficiency, approximately 92%.
- Fastening to heat sink with or without PU foam adhesive tape of automotive grade, please select which suits the best for your needs.
- We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the tape.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_TAPE.pdf)


LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Strada-DW-GD	C11132_Strada-DW-GD	±48° - ±74°
Strada-DW-GD-TAPE	CA11180_Strada-DW-GD-tape	±48° - ±74°

EULUMDAT & IES FILES AVAILABLE BY REQUEST

MEASUREMENT DATA

Relative Intensity of C11132_Strada-DW-GD




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2011-03-08

DRAWING



© Ledil Oy – PRELIMINARY - Subject to change without prior notice