



Description

American Beauty offers the widest selection of resistance soldering handpieces in the world. Our hand pieces are designed and built to provide absolute performance in even the toughest environments. By generating heat instantaneously and right at the point of contact, you are able to easily handle the historically difficult soldering jobs.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 10552 featured on this page:

Model	Product Name	
10515	3/32" Probe Style Handpiece	

Replacement Products

The following products can be used as replacements for Model 10552 featured on this page:

Model	Product Name	
10582	5/64" Steel Electrodes for Resistance Soldering	

Applications

Users of this product have stated that they use it for several jobs which include but are not limited to:

1. Soldering flat plated copper

Technical Specifications

RoHS Compliant	Yes
Connection Type	Tapered Pins
Electrode Size/Diameter	.078 in / 0.20 cm
Country of Origin	US
Package Length	9.50 in / 24.13 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.40 lbs / 0.18 kg

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits

Copper-coated, stainless steel electrodes can be easily bent, allowing the user to customize the handpiece to their specific application.