

**ACCESSORIES 10 (3/8")**
**3019**
**CONVERTOR 3/8" TO 1/2"**

- ▀ Acc. to DIN 3123, ISO 3316
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated

**10**  
**3/8"**  
**12,5**  
**1/2"**


Code	No.	□ "	□	■ "	■	□ mm □	□	□	£
6236010	<b>3019</b>	3/8	10	1/2	12.5	35	53	10	

**10**  
**3/8"**
**3020**
**REDUCER 3/8" TO 1/4"**

- ▀ Acc. to DIN 3123, ISO 3316
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated

**10**  
**3/8"**  
**6,3**  
**1/4"**


Code	No.	□ "	□	■ "	■	□ mm □	□	□	£
6236280	<b>3020</b>	3/8	10	1/4	6,3	28,5	26	10	

**10**  
**3/8"**
**3081**
**L-HANDLE 3/8"**


- ▀ Acc. to DIN 3122, ISO 3315
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated

**10**  
**3/8"**


Code	No.	■ "	■	□ mm □	□	□	£
6236360	<b>3081</b>	3/8	10	180	153	10	

**10**  
**3/8"**
**3084**
**SPEED BRACE 3/8"**

- ▀ Acc. to DIN 3122, ISO 3315
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated
- ▀ No. 3084 L for applications e.g. in the aviation sector

**10**  
**3/8"**


Code	No.	■ "	■	□ mm □	□	□	£
6236440	<b>3084</b>	3/8	10	288	423	10	
1965395	<b>3084 L</b>	3/8	10	463	568	1	

**10**  
**3/8"**
**3087**
**SLIDING T BAR 3/8"**

- ▀ Acc. to DIN 3122, ISO 3315
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated



Code	No.	■ "	■	□ mm □	□	□	£
6236520	<b>3087</b>	3/8	10	163	164	5	

**10**  
**3/8"**
**3087 A**
**SLIDING T BAR WITH RELEASE 3/8"**


- ▀ Secured against unintentional removal
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated
- ▀ Turn handle for easy locking and releasing
- ▀ Accidental release when working is prevented because of the asymmetrical release point
- ▀ Particularly useful for work in sensitive areas where certainty against loss is a theme
- ▀ Examples: Aircraft engine, work in deep machine bodies
- ▀ DBGM (German utility patent)



Code	No.	■ "	■	□ mm □	□	□	£
1871633	<b>3087 A</b>	3/8	10	163	135	1	

**10**  
**3/8"**
**3090**
**EXTENSION 3/8"**

- ▀ Acc. to DIN 3123, ISO 3316
- ▀ For hand-operated sockets and accessories with square drive as per DIN 3120, ISO 1174, with ball locking device
- ▀ GEDORE vanadium steel 31CrV3, polished, chrome-plated
- ▀ \* not standardised



Code	No.	*	■ "	■	□ mm □	□	□	£
1476637	<b>3090-2</b>	*	3/8	10	50	63	5	
6236600	<b>3090-3</b>		3/8	10	76	93	5	
6236790	<b>3090-5</b>		3/8	10	125	117	5	
1476645	<b>3090-7</b>	*	3/8	10	180	164	5	
6236870	<b>3090-10</b>		3/8	10	250	222	5	
6238570	<b>3090-12</b>	*	3/8	10	305	287	5	
1476653	<b>3090-20</b>	*	3/8	10	500	524	1	