


Metric cheese head slotted machine screws - Slotted



DIN 84
BS 4183
ISO 1207

Materials/Finishes:

Steel 4.8/Zinc & clear
Stainless steel/Self colour
Brass/Self colour

Dimensions

Thread (d)	M2	M2.5	M3	M3.5	M4	M5	M6	M8
D max	3.8	4.5	5.5	6	7	8.5	10	13
H nom	1.3	1.7	2	2.4	2.6	3.3	3.9	5
w (slot width) nom	0.7	0.8	1	1.1	1.3	1.3	1.8	2.1
t (slot depth) nom	0.75	0.8	0.9	1	1.1	1.3	1.6	2

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

Preferred lengths

		Thread (d)							
		M2	M2.5	M3	M3.5	M4	M5	M6	M8
Length (L)	4	ST	ST						
	5	ST	ST	ST BR					
	6	ST	ST	ST BR		ST BR			
	8	ST	ST	ST BR		ST BR	ST BR		
	10	ST	ST	ST BR		ST BR	ST BR	ST	
	12	ST	ST	ST BR		ST BR	ST BR	ST BR	
	16	ST		ST BR		ST BR	ST BR	ST BR	
	20	ST		ST BR		ST BR	ST BR	ST BR	
	25			ST BR		ST BR	ST BR	ST BR	
	30			ST		ST	ST	ST	
	35			ST		ST	ST	ST	
	40			ST		ST	ST	ST	
	45								

	50								
	60								
	65								
	70								

ST - Steel, Zinc & clear - other finishes often available

BR - Brass, Self colour