THIS DRAWING IS UNPUBLISHED
VERTRAULICHE UNVEROEFFENTLICHE ZEICHNUNG
RELEASE FOR PUBLIKATION ,2000
FREI FUER VEROEFFENTLICHUNG
© COPYRIGHT 2000 BY AMP INCORPORATED ALL RIGHTS RESERVED
ALLE RECHTE VORBEHALTEN

MATED WITH:
PASSEND ZU:
HA.3/4

LOC	DIST
AI	-

PROJEKT NR. -

REVISIONS
AENDERUNGEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	C1	PRINTING CORRECTED ECR-06-021058	01.09.2006	SR	SM
	C2	ECR-10-000005	09FEB10	RK	SRE

CONTACT ARRANGAMENT
VIEV FROM CONECTING SIDE



LATERAL PRINT
PN 1-1





LATERAL PRINT
PN 0-1



LATERAL PRINT
PN 0-2



CONTACT ARRANGAMENT
VIEV FROM TERMINATION SIDE





NOTES

1 CONTACT: 1 TO 4
SUITABLE SCREW CONTACTS: SERIES HA.3
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,4 MM

△2 GROUNDING CONTACT:
SUITABLE SCREW CONTACTS: SERIES HA.4
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,4 MM

3 SUITABLE HOOD SIZE 1: SERIES HA; HD; EMV AND HIP

4 SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 2,0x65

5 STANDARDS:
DIN EN 61984; DIN EN 60664-1

△6 POLARIZATION RIPS

△7 POS. 8 AND POS.9 PACKED SEPARATE IN POLY BAG

8 AUTHORIZATION: UL; CSA; VDE; SEV

9 PACKAGING:
10 SETS IN A CARTON, PRE-MOUNTED

OBSOLETE

0-2	0-1	1-1	DESCRIPTION	MATERIAL	COLOR	SURFACE	ITEM	NOTES
			HA.4.Bu.S					
			HA.4.Bu.S-Au					
HA.4.Bu.S								
	1	1	SPRING WASHER	STEEL		ZINK PLATED	9	V3.2
	1	1	SLOTED COUNTER FLAT HEAD SCREW	STEEL		ZINK PLATED	8	M3x8
5	5	5	SLOTED CHEESE HEAD SCREW	BRASS		NICKEL PLATED	7	M3x5.5
	1		CONTACT SOCKET	BRASS		GOLD PLATED	6	
1		1	CONTACT SOCKET	BRASS		SILVER PLATED	5	
	4		CONTACT SOCKET	BRASS		GOLD PLATED	4	
4		4	CONTACT SOCKET	BRASS		SILVER PLATED	3	
1	1	1	COVER	LEXAN	BEIGE		2	
1	1	1	MALE INSERT	LEXAN	BEIGE		1	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. AENDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWEILS LETZTGUELTIGEN AENDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.

DIMENSIONS: DIMENSIONEN: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN
n. ISO 8015 -
n. ISO 2768 - m H-E
n. DIN 16901- 140
0 PLC #
1 PLC #
2 PLC #
3 PLC #
ANGLES / WINKEL #

MATERIAL

FINISH / OBERFLAECHE / FARBE

DWN H.BRAUN 29.07.1997
CHK KRAMER 29.07.1997
APVD T.SCHNURPFEIL 28.03.2006
PRODUCT SPEC. PRODUKTSPEZ. 108-74008
APPLICATION SPEC. VERARBEITUNGSSPEZ. 114-74010
WEIGHT GEWICHT 0,0013 KG

Tyco Electronics
Tyco / Electronics AMP GmbH
D - 53819 Neunkirchen

NAME
FEMALE INSERT
HA.4.BU.S

SIZE A2 | CAGE CODE 00779 | DRAWING NO ZEICHNUNGS-NR. C- 1103403 | RESTRICTED TO NUR FUER

CUSTOMER DRAWING / KUNDENZEICHNUNG

SCALE MASSSTAB 1:1 | SHEET BLATT 1 OF VON 1 | REV. C2

This is a TRANSLATED file from Computervision, Inc., Medusa Revision 12.2.3T