


DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE

PROJECTION



NOTES:

- 1 FOR STRIP VERSION SEE DWG. 166047.
2 UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
ZONE I : BRIGHT TIN/LEAD PLATED.

WIRE RANGE :
(0,05-0,14mm²) 26-30 AWG
INSULATION RANGE :
1,22 MAX. DIA.

-	-	-	-
-	-	-	-
STAINLESS STEEL	SEE NOTE 2	BRASS	166297-1
MATERIAL OF SLEEVE	PLATING OF BODY	MATERIAL OF BODY	PARTNUMBER
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
A	EH-0077-92	JvL	CvT 04-03-94
LTR.	REVISION RECORD	DR.	CHK. DATE
DR. : J.V.LIEMPT	CHK. : C.v.TILBURG	APP. : L.v.SOEST	DWG.No. C-166297
DATE, 6 JAN 1993	DATE, 08-02-93	DATE, 08-02-93	REV.LTR. A
SHEET 1 OF 1			A3

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATED
© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION, 19-

AMP

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME

CONTACT ASSEMBLY-PIN
TYPE XI, SIZE 20 LOOSE PIECE