






NOTES:

1. Dimensions are in inches & [mm].
2. Socket body: Glass-filled polyester, 94 VO rating, green in color
3. Receptacle shell: 360 brass, with 200 μ in tin over 100 μ in nickel
4. Receptacle contacts: Beryllium copper with 30 μ in gold over 50 μ in nickel
5. The continuous temperature rating of the socket shall be 150° C.
6. Contact resistance: 20 milliohms or less.



DETAIL A
SCALE 2:1



SECTION A-A

TOLERANCES - UNLESS OTHERWISE SPECIFIED
 .XX = ±.01 [254]
 .XXX = ±.005 [127]
 ANG. = ±5°



TITLE: POWER DIP SOCKET
 SUBJECT: MECHANICAL DRAWING
 ENGINEER: D-M
 DRAWN BY: R.MOR
 DCL: 13242
 SHL 1 OF 1

MODEL: MS05
 REV: F
 DATE: 03JUN13