






NOTES:

1. MATERIAL: STEEL, ANNEALED, .020±.001 THICK
2. PLATING: .000200 IN. MIN. BRIGHT TIN OVER .000100 IN. MIN. COPPER OVERALL.
3. PRODUCT CONFORMS TO PRODUCT SPECIFICATION PS-71182.
4. PACKAGING: PRODUCT IS BULK PACKAGED



SECTION A-A

PART #	CABLE DIA. RANGE	"C"	"D"	"E"	"F"	USES EMI CAN KIT NUMBER
73772-0001	.246-.321 (6.25-8.16)	.324 (8.23)	.437 (11.10)	.450 (11.43)	.191 (4.85)	71755-1001 88789-9332 88789-9333
73772-0002	.322-.354 (8.17-9.00)	.375 (9.53)	.437 (11.10)			
73772-0003	.355-.387 (9.01-9.84)	.392 (9.96)	.505 (12.83)	.565 (14.35)	.235 (5.97)	71755-1000 88789-9333
73772-0004	.388-.420 (9.85-10.67)	.432 (10.97)	.505 (12.83)			71755-1000

ADDED KIT #S EC No. UDT2001-0277 DRWS: TMCCLMIDCA 0000905 CHKs: TMCLELL 0000906 APPR: NELSON 0000907 CI	DESCRIPTION REV	QUALITY SYMBOLS MAJOR CRITICAL	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 5 : 1	DESIGN UNITS ☐ mm ☒ INCH	THIRD ANGLE PROJECTION ☐ mm ☒ INCH ☐ mm ONLY		DIMENSIONS: ☐ mm ☒ INCH ☐ mm ONLY		SHT	REV		
											REVISE ON CAD ONLY			
					mm	INCH	DRAWN BY & DATE PMURPHY 97/03/26		TITLE: MICROCROSS, P&D AND DVI					
					4 PLACES	±0.	±.	CHECKED BY & DATE JNELLIGA 97/03/26		CRIMP FERRULES				
					3 PLACES	±0.---	±.015	APPROVED BY & DATE JNELLIGA 97/03/26		SALES DRAWING				
					2 PLACES	±0.38	±.			MOLEX INCORPORATED				
					1 PLACE	±0.	±.	CAD FILENAME 73772S1.DGN		MATERIAL NO.		DRAWING NO.	SHEET N	
					ANGULAR: ± 1/2°				SEE CHART		SD-73772-000		1 OF 1	
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							SIZE