


**HIGH THERMAL AND DIELECTRIC PERFORMANCE INSULATOR PAD**

Tgard™ K52 is a high thermal and dielectric performance insulator pad consisting of a ceramic filled phase change compound coated on MT Kapton film.

Tgard™ K52 phase change coating all but eliminates contact thermal resistance. The phase change coating melts at 52°C and replaces all contact areas that contain air. Tgard™ K52-1 is ideal for applications requiring the best thermal performing insulator material.

Tgard™ K52-2 has the best balance of thermal, dielectric and cut through performance. Tgard™ K52-3 is a 3 mil MT Kapton film that provides the best crush and cut and tear resistance available with thermal properties that are still in the high performance category.

FEATURES AND BENEFITS

- High breakdown voltage of 4,000 – 9,000 range VAC
- Resistant to tears and cut through
- Total thermal resistance of 0.13 - 0.30 range °C-in²/watt at 20 psi clip force

APPLICATIONS

- Audio amps
- Power modules
- Switching mode power supplies

global solutions: local support™

Americas: +1.800.843.4556

Europe: +49.8031.2460.0

Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com

www.lairdtech.com/thermal

Tgard™ K52

Thermally Conductive Insulators

PROPERTY	TEST METHOD	K52-1	K52-2	K52-3
ELECTRICAL PROPERTIES				
Dielectric With Standard Voltage 50mm probe for 30 sec.	ASTM D149	3,000 volts AC	6,000 volts AC	7,500 volts AC
Dielectric Breakdown Voltage 50mm probe	ASTM D149	4,200 volts AC	7,800 volts AC	9,000 volts AC
Volume Resistivity	ASTM D257	4 x 10 ¹⁴	4 x 10 ¹⁴	4 x 10 ¹⁴
Dielectric Constant @ 1 MHz	ASTM D257	1.8	1.8	1.8
MECHANICAL PROPERTIES				
Composite Thickness	ASTM D374	2 mil (0.051mm)	3 mil (0.076mm)	4 mil (0.102mm)
MT Kapton® Thickness	ASTM D374	1 mil (0.025mm)	2 mil (0.051mm)	3 mil (0.076mm)
Tensile Strength	ASTM D412	13.5 kpsi (93 mPa)	18 kpsi (124 mPa)	20 kpsi (139 mPa)
Elongation MD	ASTM D412	80%	80%	80%
Operating Temperature Range		-60 - 150°C	-60 - 150°C	-60 - 150°C
Color		Light amber	Light amber	Medium amber

PRESSURE, PSI (KPA)	10 (69)	20 (138)	50 (345)	100 (689)	200 (1379)	400 (2758)
TOTAL THERMAL RESISTANCE						
K52-1	0.14 (0.90)	0.14 (0.90)	0.13 (0.84)	0.13 (0.84)	0.13 (0.84)	0.13 (0.84)
K52-2	0.23 (1.48)	0.23 (1.48)	0.22 (1.42)	0.22 (1.42)	0.22 (1.42)	0.22 (1.42)
K52-3	0.33 (2.13)	0.32 (2.06)	0.31 (2.00)	0.30 (1.94)	0.30 (1.94)	0.30 (1.94)

STANDARD DIE CUT PARTS:	Standard part sizes for TO-220, TO-247, TO-3P, TO-3PL, and TO-264
CUSTOM DIE CUT PARTS:	Custom configurations available with standard tolerance of 0.5mm (0.020") Ability to handle drawings in multiple file formats. (.DXF and .DWG preferred)
PRESSURE SENSITIVE ADHESIVE:	Single side adhesive available on request

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

THR-DS-Tgard-K52 0710

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2010 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trade marks or registered trade marks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights. A14644-00 REV D