







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
H	—		R	EH-1477-98	14-09-98	EVE —
			R1	ECR-08-012368	06-11-08	AEG WRV
			R2	ECR-10-022530	07JAN11	KK HMR

NOTES:

1. TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15$.
2. MODULAR JACK P.N. 216446-1, 216446-2, 3-216446-1 AND 3-216446-2 ARE DELIVERED WITH PLASTIC SOLDER STOP INSTALLED, TO PREVENT SOLDER ENTERING THE JACK. REMOVE SOLDER STOP AFTER SOLDERING.
3. FOR PERFORMANCE REQUIREMENTS SEE TE PRODUCT SPECIFICATION 108-19064.
4. FOR APPLICATION REQUIREMENTS SEE TE APPLICATION SPECIFICATION 114-19019.
5. MOLDED-IN CHARACTER "1,6" MEANS FOR 1,6mm PRINT THICKNESS.
6. FOR PACKAGING SEE SHEET 2.
7. PREFERRED DIRECTION FOR STAMPING OF HOLE TO OBTAIN A BROKEN EDGE AT JACK ENTRY SIDE.
8. TRUE POSITIONING OF THE SOLDER TINES MAY BE AFFECTED BY BULK PACKAGING. THE SOLDER STOP COULD BE LOOSENED DURING TRANSPORT.



OBSOLETE	6 POS./4 CONTACTS WITH SOLDER STOP	CONTACTS:	HOUSING:	3-216446-2
	6 POS./6 CONTACTS WITH SOLDER STOP	1,25µm MIN. GOLD OVER	20% G.F. NYLON	3-216446-1
	6 POS./4 CONTACTS WITH SOLDER STOP	1,25µm MIN. NICKEL IN CONTACT AREA	COLOR: BLACK UL 94-HB	216446-2
	6 POS./6 CONTACTS WITH SOLDER STOP	2µm MIN. TIN LEAD OVER 1,25µm MIN. NICKEL ON SOLDER TINES.	CONTACTS: PHOS. BRONZE	216446-1
DESCRIPTION		FINISH	MATERIAL	PARTNUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.V.ESSSEN 29NOV95	TE Connectivity	
DIMENSIONS: mm		CHK W.BRUMMANS		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.V.TILBURG	NAME	
0 PLC ± -		PRODUCT SPEC		
1 PLC ± -		APPLICATION SPEC	MODULAR JACK, 6 POS BOTTOM ENTRY VERSION FOR PRINTED CIRCUIT BOARD MOUNTING	
2 PLC ± -		—		
3 PLC ± -		—	SIZE	CAGE CODE
4 PLC ± -		—	A2	00779
ANGLES ± -		WEIGHT	SCALE	SHEET
FINISH		CUSTOMER DRAWING	NTS	1 of 2
			REV	R2

LOC	DIST	REVISIONS			
H	-	P	LTR	DESCRIPTION	DATE
		-		SEE SHEET 1	-

D

C

B


A

D

C

B

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F.V.EIJK	19DEC96	TE Connectivity	
DIMENSIONS: mm		CHK W.BRUMMANS	-		
		APVD R.SMEETS	-	NAME	
		PRODUCT SPEC	-	MODULAR JACK, 6 POS., BOTTOM ENTRY VERSION PACKAGING	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-	SIZE	RESTRICTED TO
0 PLC ± -		WEIGHT	-	A2	-
1 PLC ± -		CUSTOMER DRAWING		CAGE CODE	REV
2 PLC ± -		SCALE		00779	2 OF 2
3 PLC ± -		SHEET		C=216446	R2
4 PLC ± -		REVISIONS			
ANGLES ± -					
FINISH					
-					