

EPIC® HA series

Compact screw-terminated inserts for medium power & control applications



Similar to the HBE series inserts but more compact, EPIC® HA series inserts are used whenever space is limited. EPIC® HA 3/4 inserts and housings provide the smallest possible footprint in a 10A power connector. HA 10-48 inserts are unique because of their shortened ground straps, which still allow for a wire cross-section up to 2.5 mm². HA 3-48 screw-terminated inserts fit into EPIC® HA series housings. A modified EPIC® HB 48 housing can fit 64 contacts.

Technical data


Number of contacts:	3, 4, 10, 16, 32, 48, 64 (+PE)	Rated current:	
Temperature range:	-40°C to +100°C	- UL:	
- short-term:	up to +125°C	- EPIC® HA 3/4:	10A
Pollution level:	3	- EPIC® HA 10 - 64:	14A
Dimensioning transient:	4 kV	- CSA:	
Mating cycles:	- per DIN EN 61984:2008 Service Life Test: Tested to 100 cycles and passed - per Contact Thermal Test: Useful service up to 500 cycles is possible at rated voltage and current*	- EPIC® HA 3/4:	10A
Test voltage:	4 kV	- EPIC® HA 10 - 64:	16A
Rated voltage:		- IEC:	
- UL:	600V	- EPIC® HA 3/4:	23A
- CSA:	600V	- EPIC® HA 10 - 64:	16A
- IEC:		- SEV:	16A
- EPIC® HA 3/4:	400V	Wire size:	
- EPIC® HA 10 - 64:	250V	- EPIC® HA 3/4:	
- SEV:	250V	- solid or stranded wire with ferrule:	20 - 14 AWG (0.5 - 2.5 mm²)**
		- EPIC® HA 10 - 64:	
		- solid or stranded wire with ferrule:	20 - 14 AWG (0.5 - 2.5 mm²)**
		- for stranded wire without ferrule:	18 - 14 AWG (0.75 - 2.5 mm²) (requires insert with wire protection)
		Contact material:	silver-plated copper alloy
		Contact resistance:	1.5 - 4 mΩ

* In dry, non-conductive, non-corrosive environments when protected in a housing rated at least IP54 and disconnected for cycling and maintenance only.


** May be limited, depending on the ferrule crimp profile.

EPIC® HA derating curves

16 AWG (1.5 mm²)



14 AWG (2.5 mm²)





HA series


Rectangular connector inserts

EPIC® HA 3

screw termination: 600V, 10A



all dimensions are in mm



view from cable side

Termination	Plug	Receptacle
screw termination	10420000	10421000

Complete the installation

Coding pin:
10451400

Compatible housing



HA 3/4
page 413

Approvals




EPIC® HA 4

screw termination: 600V, 10A



all dimensions are in mm



view from cable side

Termination	Plug	Receptacle
screw termination	10431000	10432000

Complete the installation

Coding pin:
10451400

Compatible housing



HA 3/4
page 413

Approvals




EPIC® HA 10

screw termination: 600V, 14A



all dimensions are in mm



view from cable side

Termination	Wire protection	Plug	Receptacle
screw termination	yes	10440100	10441100
screw termination	no	10440000	10441000

Compatible housing



HA 10
page 415

Approvals




EPIC® HA 16

screw termination: 600V, 14A



all dimensions are in mm



view from cable side

Termination	Wire protection	Plug	Receptacle
screw termination	yes	10530000	10531000
screw termination	no	10532000	10533000

Compatible housing



HA 16
page 417

Approvals




EPIC® HA 32

screw termination: 600V, 14A



all dimensions are in mm



view from cable side

Termination	Wire protection	Contact numbering	Plug	Receptacle
screw termination	yes	# 1 - 16	10530000	10531000
screw termination	yes	# 17 - 32	10540000	10541000
screw termination	no	# 1 - 16	10532000	10533000
screw termination	no	# 17 - 32	10542000	10543000

Compatible housing

HA 32
page 419

Approvals





HA series


Rectangular connector inserts

EPIC® HA 48

screw termination: 600V, 14A



all dimensions are in mm



view from cable side

Termination	Wire protection	Contact numbering	Plug	Receptacle
screw termination	yes	#1 - 16	10530000	10531000
		#17 - 32	10540000	10541000
		#33 - 48	10540100	10541100
screw termination	no	#1 - 16	10532000	10533000
		#17 - 32	10542000	10543000
		#33 - 48	10542100	10543100

Compatible housing


HA 48
page 421

Approvals




EPIC® HA 64

screw termination: 600V, 14A



all dimensions are in mm



view from cable side

Termination	Wire protection	Contact numbering	Plug	Receptacle
screw termination	yes	#1 - 16	10530000	10531000
		#17 - 32	10540000	10541000
		#33 - 48	10540100	10541100
		#49 - 64	105300LE64	105310LE64

Compatible housing

HA 64
page 422

Approvals

