



Magnetic Mounts

Stock Locator

- Corrosion resistant materials used throughout for high durability and weather resistance
- Neoprene seal for moisture protection
- High 80lb pull strength will allow antenna to stay put
- Optional rubber boot provides additional protection to mounting surface
- Triple reinforced coax strain relief eliminates cable pull out

Results 1 - 37 of 37

Item #	Model	Color	Cable Length	Cable	Connector Type
G8	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	N/A
G8B	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	BNC Crimp
G8BI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	BNC Crimp, Installed
G8MI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	Mini UHF Crimp, Installed
G8N	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	N Crimp
G8NS	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	N Solder
G8P	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	UHF (PL259) Crimp
G8PI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	UHF (PL259) Crimp, Installed
G8PS	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	UHF (PL259) Solder
G8PST	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	UHF (PL259) Teflon® Solder
G8TI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	TNC Crimp, Installed
G8U	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	N/A
G8UB	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	BNC Crimp
G8UM	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	Mini UHF Crimp
G8UN	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	N Crimp
G8UNS	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	N Solder
G8UP	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	UHF (PL259) Crimp
G8UPST	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	UHF (PL259) Teflon® Solder
G8UT	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58U Solid Center Conductor Cable	TNC Crimp
G8X	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	N/A
G8XBI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	BNC Crimp, Installed

G8XM	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	Mini UHF Crimp
G8XNI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	N Crimp, Installed
G8XNS	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	N Solder
G8XP	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	UHF (PL259) Solder
G8XPST	3/4" Style Magnetic Mounts	Chrome	12 ft	RG8X Low Loss Cable	UHF (PL259) Teflon® Solder
GB8	3/4" Style Magnetic Mounts	Black	12 ft	RG58A/U Stranded Center Cable	RG58A/U
GBR8PI	3/4" Style Magnetic Mounts	Black	12 ft	RG58A/U Stranded Center Cable	Rubber Boot Option - RG58A/U with PL259 Installed
GD	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	N/A
GDBI	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	BNC Crimp, Installed
GDM	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	Mini UHF Crimp
GDNI	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	N Crimp, Installed
GDNS	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	N Solder
GDPI	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	UHF (PL259) Crimp, Installed
GDPST	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	UHF (PL259) Teflon® Solder
GDT	3/4" Style Magnetic Mounts	Chrome	12 ft	Teflex™ Cable	TNC Crimp
GR8PI	3/4" Style Magnetic Mounts	Chrome	12 ft	RG58A/U Stranded Center Cable	UHF (PL259) Crimp, Installed

Results 1 - 37 of 37