

T&B® Fittings



T&B Catalog Number: EFC150
UPC Number: 78621078965
Description: 1 1/2" Black Corrugated PVC flexible tubing. For use with Bullet™ Liquidtight Fittings.

Status: Active



WEB_USE

-T&B Product Line 012

Features

- Maximum flexibility in tight applications.
- Extremely fast installation
- Liquidtight with specified fittings.
- Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

General

- Material PVC
- Color Black
- Recommended industrial applications Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship-board wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

Dimension Information

- I.D. - Minimum (inches) 1.575
- I.D. - Maximum (inches) 1.600
- O.D. - Minimum (inches) 1.865
- O.D. - Maximum (inches) 1.900
- Conduit Size (inches) 1 1/2

Packaging

- T&B Order Multiple 50
- Package in Units 50
- T&B Sold in UOM Feet
- T&B Weight Per UOM 36.8 lbs. per 100

Application Support

- Guide to Nonmetallic Conduit Applications Available on Website
- XTRAFLEX System Specifications Available on Website

Notes

- *Note OEM Grade U.L. Recognized
- **Note Broad operating temperature range - 18° C to +60° C (-2° F to +140° F)
- ***Note Flammability rating VW-1 (vertical wire) UL 224.

Certifications

- RoHS Compliance Yes

Certifications



File Nbr:

E 96548

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com