



NOTES:

1. MAX. MOUNTING TORQUE = 6 lb-in.
2. HARDWARE IS INCLUDED.



LEAD FINISH:	SOLDER
BUSHING FINISH:	SILVER
CAPACITANCE	5500pF $\diamond$ 28
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C 300 VDC -----
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
50	50
100	65
1 GHz	70

SCHEMATIC



MARKING: PART: M15733/46-0001
 BAG: MIL 15733/46-0001
 OLSP2
 DATE CODE
 300VDC
 +125°C
 10 AMPS
 QTY./BAG (100 MAX.)
 P.O. NO.

NOTE: PACKAGE MARKED SAME AS BAG.

	28	27	26	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA	
	CN 208159	CN 205524	CN 185108	CHANGE NOTICE	Fractions $\pm 1/64$ Dec. .xx $\pm$ Dec. .xxx $\pm .010$ Angles $\pm 0^\circ 30'$			
					CODE IDENT. NO. OLSP2	Dwn. KAUFFMAN DATE 7/29/02 Ckd. * Scale NONE	Description Pi RESIN SEAL FILTER	51-709-004