THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| FT | 0 |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | T3 | REVISED PER ECO-13-008672 | 30AUG2013 | KH | DR |













## RECOMMENDED PANEL CUTOUT

| | L | B | A | MATERIAL | PART NUMBER |
|---|---|---|---|---|---|
| | 14.07 [.554] | 3.99 [.157] | 42.82 [1.686] | 1 | 1-201357-1 |
| | 14.07 [.554] | 3.99 [.157] | 42.82 [1.686] | 1 | 1-201357-0 |
| OBSOLETE | 14.07 [.554] | 3.86 [.152] | 43.08 [1.696] | 2 | 201357-9 |
| | 14.07 [.554] | 3.86 [.152] | 43.08 [1.696] | 2 | 201357-3 |
| | 11.79 [.464] | 3.99 [.157] | 42.82 [1.686] | 1 | 201357-1 |

1 PHENOLIC, BLACK.

2 DIALLYL PHTHALATE, BLUE.

3 MATES WITH BLOCK 200838 & ACCOMMODATES TYPE II OR TYPE III #16 PIN OR SOCKET CONTACTS. EXCEPT FOR 201357-1, WHICH ACCEPTS ONLY PIN CONTACTS.

4 FOR 201357-9, KS 21303 L9 MARKED IN ADDITION TO THE AMP PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL: SEE TABLE

FINISH: -

DWN L.SIPE 01/31/92
CHK R.STONE 2-4-92
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME: 34 POSITION MINIATURE RECTANGULAR MALE BLOCK, M SERIES

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A2 | 00779 | C-201357 | - |

CUSTOMER DRAWING

SCALE 2:1 SHEET 1 OF 1 REV T3

201357