




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
010	RELEASED	3/22/95	M.M.

DESIGN CONTROL REQUIRED

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204		
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A		
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204		
COMPONENT	MATERIAL	FINISH		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°	DRAWN BY <i>M.M.</i> DATE 3/22/95 CHECKED BY APPD BY	 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
These drawings and specifications are the property of M/A-COM Interconnect Division and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE 408-04833 (20-010) NO. AP. _____	TITLE OSM STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT		
	SIZE B	CODE IDENT NO. 26805	1250-1989-00	REV 010
	SCALE 5:1	SHEET 1 OF 1		

- NOTES:
- DESIGNED FOR USE WITH .085 DIA SEMI-RIGID CABLE
 - CAPTURED CENTER CONTACT

CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.089
CONTACT	.021

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCE ON
FRAC. DEC. ANGLES
± 1/64 ± .005 ± 1°

These drawings and specifications are the property of M/A-COM Interconnect Division and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.

USE ASS'Y PROCEDURE

408-04833
(20-010)
NO. AP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1250 1989 00](#)