

# Fixed Attenuators (SMA Type)

## AT-100, AT-200, and AT-300 Series



### ■Features

#### 1.Abundant Variations of Attenuators

Attenuation amounts are available in abundant variations from 0 to 4 dB in 0.5 dB steps, from 4 to 10 dB in 1 dB steps, and in 12, 13, 14, 15, 20, 26 and 30 dB so that levels can be finely adjusted.

#### 2.SMA Type

The coupling portions are available in all types of plug and jack combinations and stainless steel is used for the external cladding to form a small and durable structure.

#### 3.High Degree of Matching and High Reliability

The design of the attenuation element uses a distributed constant circuit and metal film resistor. A high degree of matching is achieved as indicated in the VSWR of the appended tables. Furthermore, these attenuators show stable characteristics for environments of varying temperature, humidity, and gases.

### ■Product Specifications

| Ratings | Rated frequency range (Note)<br>Characteristic impedance<br>Maximum Input Power | DC to 18.0 GHz<br>50 ohms<br>1 W | Operating temperature range<br>Operating relative humidity | -10°C to +65°C<br>95% Max. |
|---------|---------------------------------------------------------------------------------|----------------------------------|------------------------------------------------------------|----------------------------|
|---------|---------------------------------------------------------------------------------|----------------------------------|------------------------------------------------------------|----------------------------|

Note: The frequency range will differ depending on the model.

| Item                | Standard                                                                                    | Conditions                                                                                                                        |
|---------------------|---------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| 1.Vibration         | No electrical discontinuity of 1 $\mu$ s or more<br>No damage, cracks, or parts dislocation | Frequency of 10 to 2000 Hz, overall amplitude of 1.52 mm, acceleration of 98 m/s <sup>2</sup> for 2 hours in each of 3 directions |
| 2.Shock             |                                                                                             | Acceleration of 490 m/s <sup>2</sup> , sine half-wave waveform, 3 cycles in each of the 3 axis                                    |
| 3.Temperature cycle | No damage, cracks, or parts dislocation                                                     | Temperature: -55°C → +15°C to +35°C → +85°C → +15°C to +35°C<br>Time: 30 → 15 max. → 30 → 15 max. (Minutes)<br>5 cycles           |

●The test method conforms to MIL-STD-202.

### ■Materials

| Part                | Material         | Finish       |
|---------------------|------------------|--------------|
| Connector Body      | Stainless steel  | Passivated   |
| Insulator           | PTFE             | —            |
| Male contacts       | Beryllium copper | Gold plating |
| Female contacts     | Beryllium copper | Gold plating |
| Attenuation element | Metal film       | —            |

### ■Ordering Information

**AT - 1 00-(0) (40)**

① ② ③ ④

|                                                                                                                  |                                                                                                            |
|------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|
| ① AT: Indicates a fixed attenuator                                                                               | ③ Attenuation<br>01 : 1dB<br>06 : 6dB<br>00-(0) : 0dB<br>(Through)<br>00-(0.5) : 0.5dB<br>00-(3.5) : 3.5dB |
| ② Indicates the Series Name (Coupling Portion)<br>1: SMA plug - jack<br>2: SMA plug - plug<br>3: SMA jack - jack | ④ (40): RoHS compliant                                                                                     |


## AT-100, AT-200, and AT-300 Series Fixed Attenuators (SMA Type)

### Specifications


| Part Number      | Attenuation (dB)               |                                     | V.S.W.R.(Max) |           |           | Power (W) | Connectors | Weight (g) | RoHS |
|------------------|--------------------------------|-------------------------------------|---------------|-----------|-----------|-----------|------------|------------|------|
|                  | DC~12.4GHz                     | 12.4~18GHz                          | DC~4GHz       | 4~12.4GHz | 2.4~18GHz |           |            |            |      |
| AT-100-(0)(40)   | 0 <sup>+0.5</sup> <sub>0</sub> | 0 <sup>+1.0</sup> <sub>0</sub>      | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          | YES  |
| AT-100-(0.5)(40) | 0.5±0.5                        | 0.5 <sup>+1.0</sup> <sub>-0.5</sub> | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-101(40)       | 1±0.5                          | 1±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-100-(1.5)(40) | 1.5±0.5                        | 1.5±1.0                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-102(40)       | 2±0.5                          | 2±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-100-(2.5)(40) | 2.5±0.5                        | 2.5±1.0                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-103(40)       | 3±0.5                          | 3±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-100-(3.5)(40) | 3.5±0.5                        | 3.5±1.0                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-104(40)       | 4±0.5                          | 4±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-105(40)       | 5±0.7                          | 5±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-106(40)       | 6±0.7                          | 6±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-107(40)       | 7±0.7                          | 7±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-108(40)       | 8±0.7                          | 8±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-109(40)       | 9±1.0                          | 9±1.25                              | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-110(40)       | 10±1.0                         | 10±1.25                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-112(40)       | 12±1.0                         | 12±1.25                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-113(40)       | 13±1.0                         | 13±1.25                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-114(40)       | 14±1.2                         | 14±1.3                              | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-115(40)       | 15±1.2                         | 15±1.3                              | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-120(40)       | 20±1.2                         | 20±1.3                              | 1.15          | 1.20      | 1.30      | 1         | HRM-J・P    | 8          |      |
| AT-203(40)       | 3±0.5                          | 3±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-P・P    | 9          |      |
| AT-206(40)       | 6±0.7                          | 6±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-P・P    | 9          |      |
| AT-210(40)       | 10±1.0                         | 10±1.25                             | 1.15          | 1.20      | 1.30      | 1         | HRM-P・P    | 9          |      |
| AT-220(40)       | 20±1.2                         | 20±1.3                              | 1.15          | 1.20      | 1.30      | 1         | HRM-P・P    | 9          |      |
| AT-303(40)       | 3±0.5                          | 3±1.0                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・J    | 7          |      |
| AT-306(40)       | 6±0.7                          | 6±1.2                               | 1.15          | 1.20      | 1.30      | 1         | HRM-J・J    | 7          |      |
| AT-310(40)       | 10±1.0                         | 10±1.25                             | 1.15          | 1.20      | 1.30      | 1         | HRM-J・J    | 7          |      |
| AT-320(40)       | 20±1.2                         | 20±1.3                              | 1.15          | 1.20      | 1.30      | 1         | HRM-J・J    | 7          |      |

| Part Number | Attenuation (dB) | V.S.W.R.(Max) |        | Power (W) | Connectors | Weight (g) | RoHS |
|-------------|------------------|---------------|--------|-----------|------------|------------|------|
|             | DC~8GHz          | DC~4GHz       | 4~8GHz |           |            |            |      |
| AT-126(40)  | 26±1.0           | 1.15          | 1.20   | 1         | HRM-J・P    | 8          | YES  |
| AT-130(40)  | 30±1.2           | 1.15          | 1.20   | 1         | HRM-J・P    | 8          |      |


## External Dimensions




AT-100 Type



AT-126,130 Type













AT-200 Type




AT-300 Type

## Typical Data



## Input Power Characteristics



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Hirose Electric:

[AT-104-WP1\(40\)](#) [AT-106-WP1\(40\)](#) [AT-113-WP1\(40\)](#) [AT-115-WP1\(40\)](#) [AT-102-WP1\(40\)](#) [AT-110-WP1\(40\)](#) [AT-120-WP1\(40\)](#) [AT-109-WP1\(40\)](#) [AT-100-\(0\)-WP1\(40\)](#) [AT-101-WP1\(40\)](#) [AT-105-WP1\(40\)](#) [AT-103-WP1\(40\)](#) [AT-107-WP1\(40\)](#) [AT-108-WP1\(40\)](#)